

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276308

Luminaire Tested: P3AS13R709835DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709835DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 947.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276308

CATALOG NUMBER: P3AS13R709835DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1276308

CATALOG NUMBER: P3AS13R709835DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188055
5°	179440
10°	170716
15°	166153
20°	160034
25°	151460
30°	140857
35°	118320
40°	76257
45°	35446
50°	9279
55°	2332
60°	2324
65°	1972
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35446 cd/sqm

TEST NUMBER: P1276308

CATALOG NUMBER: P3AS13R709835DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	8.1
10°-20°	205.7	21.7
20°-30°	287.4	30.3
30°-40°	266.4	28.1
40°-50°	95.5	10.1
50°-60°	8.1	0.9
60°-70°	4.0	0.4
70°-80°	2.6	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.3	60.1
0°-40°	835.7	88.2
0°-60°	939.4	99.2
0°-90°	947.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	858	
5°	815	76
15°	732	206
25°	626	287
35°	442	266
45°	114	96
55°	6	8
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1276308

CATALOG NUMBER: P3AS13R709835DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	857.6
2.5°	844.7
5°	815.2
7.5°	787.9
10°	766.7
12.5°	749.3
15°	731.9
17.5°	710.7
20°	685.8
22.5°	657.0
25°	626.0
27.5°	594.2
30°	556.3
32.5°	507.9
35°	442.0
37.5°	358.0
40°	266.4
42.5°	181.7
45°	114.3
47.5°	63.6
50°	27.2
52.5°	9.1
55°	6.1
57.5°	5.3
60°	5.3
62.5°	4.5
65°	3.8
67.5°	3.8
70°	3.0
72.5°	3.0
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)