

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1280915

Luminaire Tested: P3AS05R15B2750DE010 E3DLD1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1280915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15B2750DE010 E3DLD1LI_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 314.0 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1280915

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1LI_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1280915

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1LI_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79204
5°	77063
10°	70406
15°	61680
20°	52901
25°	44180
30°	35347
35°	26502
40°	19236
45°	12590
50°	7880
55°	5314
60°	4693
65°	4358
70°	4103
75°	3728
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12590 cd/sqm

TEST NUMBER: P1280915

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.3	10.3
10°-20°	75.7	24.1
20°-30°	83.4	26.6
30°-40°	62.4	19.9
40°-50°	32.4	10.3
50°-60°	13.4	4.3
60°-70°	8.3	2.7
70°-80°	4.7	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.4	61.0
0°-40°	253.8	80.8
0°-60°	299.6	95.4
0°-90°	314.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	314.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	361	
5°	350	32
15°	272	76
25°	183	83
35°	99	62
45°	41	32
55°	14	13
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1280915

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1LI_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	361.2
1°	361.6
2°	360.4
3°	358.0
4°	354.4
5°	350.1
6°	344.5
7°	338.5
8°	331.4
9°	323.8
10°	316.2
12.5°	294.4
15°	271.7
17.5°	249.0
20°	226.7
22.5°	204.1
25°	182.6
27.5°	161.1
30°	139.6
32.5°	118.5
35°	99.0
37.5°	82.3
40°	67.2
42.5°	53.3
45°	40.6
47.5°	30.6
50°	23.1
52.5°	17.1
55°	13.9
57.5°	12.3
60°	10.7
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.4
72.5°	5.2
75°	4.4
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.4
90°	0.0

(END OF REPORT)