

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276355

Luminaire Tested: P3AS17R159835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 370.0 lumens
Efficiency: N/A
Efficacy: 18.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276355

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276355

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159549
5°	147457
10°	117722
15°	88922
20°	67719
25°	51608
30°	36968
35°	24119
40°	14799
45°	8931
50°	5936
55°	4588
60°	3947
65°	3424
70°	3077
75°	3050
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8931 cd/sqm

TEST NUMBER: P1276355

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.3	16.0
10°-20°	109.5	29.6
20°-30°	97.5	26.3
30°-40°	57.7	15.6
40°-50°	23.7	6.4
50°-60°	11.1	3.0
60°-70°	6.7	1.8
70°-80°	3.6	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.3	72.0
0°-40°	324.0	87.6
0°-60°	358.7	97.0
0°-90°	370.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	370.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	728	
5°	670	59
15°	392	109
25°	213	97
35°	90	58
45°	29	24
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1276355

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	727.6
1°	725.8
2°	720.4
3°	709.6
4°	691.6
5°	669.9
6°	646.5
7°	618.9
8°	590.0
9°	560.6
10°	528.7
12.5°	456.0
15°	391.7
17.5°	336.5
20°	290.2
22.5°	249.3
25°	213.3
27.5°	178.4
30°	146.0
32.5°	116.6
35°	90.1
37.5°	69.1
40°	51.7
42.5°	38.5
45°	28.8
47.5°	22.2
50°	17.4
52.5°	14.4
55°	12.0
57.5°	10.2
60°	9.0
62.5°	7.8
65°	6.6
67.5°	6.0
70°	4.8
72.5°	4.2
75°	3.6
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)