

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1280937

Luminaire Tested: P3AS05R15B2750DE010 E3DLP1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1280937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15B2750DE010 E3DLP1H_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 245.1 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1280937
CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1280937
 CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105649
5°	97644
10°	77954
15°	58888
20°	44851
25°	34163
30°	24485
35°	15981
40°	9790
45°	5923
50°	3923
55°	3058
60°	2631
65°	2283
70°	2052
75°	2033
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5923 cd/sqm



TEST NUMBER: P1280937

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	16.0
10°-20°	72.5	29.6
20°-30°	64.6	26.3
30°-40°	38.2	15.6
40°-50°	15.7	6.4
50°-60°	7.4	3.0
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.4	72.0
0°-40°	214.6	87.6
0°-60°	237.6	97.0
0°-90°	245.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	482	
5°	444	39
15°	259	73
25°	141	65
35°	60	38
45°	19	16
55°	8	7
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1280937
CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	481.8
1°	480.6
2°	477.0
3°	469.9
4°	457.9
5°	443.6
6°	428.1
7°	409.8
8°	390.7
9°	371.2
10°	350.1
12.5°	302.0
15°	259.4
17.5°	222.8
20°	192.2
22.5°	165.1
25°	141.2
27.5°	118.2
30°	96.7
32.5°	77.2
35°	59.7
37.5°	45.8
40°	34.2
42.5°	25.5
45°	19.1
47.5°	14.7
50°	11.5
52.5°	9.5
55°	8.0
57.5°	6.8
60°	6.0
62.5°	5.2
65°	4.4
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)