

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276415

Luminaire Tested: P3AS17R259835DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276415  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R259835DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 787.0 lumens  
Efficiency: N/A  
Efficacy: 38.6 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276415  
CATALOG NUMBER: P3AS17R259835DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1276415  
 CATALOG NUMBER: P3AS17R259835DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	285723
5°	274113
10°	240143
15°	193032
20°	148320
25°	112216
30°	81076
35°	53860
40°	32661
45°	19010
50°	12145
55°	9863
60°	8596
65°	7627
70°	6283
75°	6270
80°	4672
85°	6290

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19010 cd/sqm



TEST NUMBER: P1276415  
 CATALOG NUMBER: P3AS17R259835DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.4	14.4
10°-20°	235.1	29.9
20°-30°	212.6	27.0
30°-40°	127.7	16.2
40°-50°	50.7	6.4
50°-60°	23.4	3.0
60°-70°	14.3	1.8
70°-80°	7.6	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.1	71.3
0°-40°	688.8	87.5
0°-60°	763.0	96.9
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1303	
5°	1245	113
15°	850	235
25°	464	213
35°	201	128
45°	61	51
55°	26	23
65°	15	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1276415  
CATALOG NUMBER: P3AS17R259835DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1303.0
1°	1303.0
2°	1296.9
3°	1283.4
4°	1266.2
5°	1245.3
6°	1218.3
7°	1187.7
8°	1152.1
9°	1116.5
10°	1078.5
11°	1034.3
12°	988.9
13°	943.5
14°	898.1
15°	850.3
17.5°	737.4
20°	635.6
22.5°	543.5
25°	463.8
27.5°	388.9
30°	320.2
32.5°	257.7
35°	201.2
37.5°	153.4
40°	114.1
42.5°	83.4
45°	61.3
47.5°	46.6
50°	35.6
52.5°	29.4
55°	25.8
57.5°	22.1
60°	19.6
62.5°	16.0
65°	14.7
67.5°	12.3
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	3.7
82.5°	2.5
85°	2.5
87.5°	1.2



TEST NUMBER: P1276415  
CATALOG NUMBER: P3AS17R259835DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)