

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276417

Luminaire Tested: P3AS17R259835DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276417  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R259835DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1284.0 lumens  
Efficiency: N/A  
Efficacy: 62.9 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276417  
CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276417

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	823640
5°	768433
10°	615575
15°	417846
20°	252839
25°	147855
30°	84190
35°	46311
40°	24589
45°	12932
50°	7539
55°	5620
60°	4824
65°	5085
70°	4744
75°	4151
80°	3157
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12932 cd/sqm



TEST NUMBER: P1276417  
 CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	309.8	24.1
10°-20°	506.0	39.4
20°-30°	289.2	22.5
30°-40°	114.1	8.9
40°-50°	35.0	2.7
50°-60°	13.8	1.1
60°-70°	9.3	0.7
70°-80°	5.2	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.0	86.1
0°-40°	1219.1	94.9
0°-60°	1267.9	98.7
0°-90°	1284.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3756	
5°	3491	310
15°	1841	506
25°	611	289
35°	173	114
45°	42	35
55°	15	14
65°	10	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1276417

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3756.1
1°	3748.7
2°	3718.0
3°	3664.1
4°	3589.2
5°	3491.0
6°	3375.7
7°	3245.6
8°	3094.7
9°	2940.1
10°	2764.6
11°	2591.6
12°	2401.4
13°	2213.7
14°	2021.0
15°	1840.6
17.5°	1427.1
20°	1083.5
22.5°	813.6
25°	611.1
27.5°	452.8
30°	332.5
32.5°	240.5
35°	173.0
37.5°	122.7
40°	85.9
42.5°	58.9
45°	41.7
47.5°	29.4
50°	22.1
52.5°	17.2
55°	14.7
57.5°	13.5
60°	11.0
62.5°	9.8
65°	9.8
67.5°	8.6
70°	7.4
72.5°	6.1
75°	4.9
77.5°	3.7
80°	2.5
82.5°	2.5
85°	1.2
87.5°	1.2



TEST NUMBER: P1276417  
CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)