

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276418

Luminaire Tested: P3AS17R259835DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259835DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 787.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276418

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1276418

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285723
5°	274113
10°	240143
15°	193032
20°	148320
25°	112216
30°	81076
35°	53860
40°	32661
45°	19010
50°	12145
55°	9863
60°	8596
65°	7627
70°	6283
75°	6270
80°	4672
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19010 cd/sqm

TEST NUMBER: P1276418

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	14.4
10°-20°	235.1	29.9
20°-30°	212.6	27.0
30°-40°	127.7	16.2
40°-50°	50.7	6.4
50°-60°	23.4	3.0
60°-70°	14.3	1.8
70°-80°	7.6	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.1	71.3
0°-40°	688.8	87.5
0°-60°	763.0	96.9
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1303	
5°	1245	113
15°	850	235
25°	464	213
35°	201	128
45°	61	51
55°	26	23
65°	15	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1276418

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1303.0
1°	1303.0
2°	1296.9
3°	1283.4
4°	1266.2
5°	1245.3
6°	1218.3
7°	1187.7
8°	1152.1
9°	1116.5
10°	1078.5
11°	1034.3
12°	988.9
13°	943.5
14°	898.1
15°	850.3
17.5°	737.4
20°	635.6
22.5°	543.5
25°	463.8
27.5°	388.9
30°	320.2
32.5°	257.7
35°	201.2
37.5°	153.4
40°	114.1
42.5°	83.4
45°	61.3
47.5°	46.6
50°	35.6
52.5°	29.4
55°	25.8
57.5°	22.1
60°	19.6
62.5°	16.0
65°	14.7
67.5°	12.3
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	3.7
82.5°	2.5
85°	2.5
87.5°	1.2



TEST NUMBER: P1276418

CATALOG NUMBER: P3AS17R259835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)