

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276450

Luminaire Tested: P3AS17R309835DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309835DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276450
CATALOG NUMBER: P3AS17R309835DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1276450
 CATALOG NUMBER: P3AS17R309835DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270307
5°	261875
10°	235956
15°	195188
20°	151120
25°	113353
30°	82291
35°	54823
40°	33692
45°	19785
50°	12145
55°	9863
60°	8596
65°	7005
70°	6283
75°	6270
80°	4672
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19785 cd/sqm



TEST NUMBER: P1276450
 CATALOG NUMBER: P3AS17R309835DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.4	13.8
10°-20°	236.8	29.9
20°-30°	215.4	27.2
30°-40°	130.3	16.5
40°-50°	52.2	6.6
50°-60°	23.1	2.9
60°-70°	13.9	1.8
70°-80°	7.6	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.7	71.0
0°-40°	691.9	87.5
0°-60°	767.3	97.0
0°-90°	791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1233	
5°	1190	109
15°	860	237
25°	468	215
35°	205	130
45°	64	52
55°	26	23
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1276450
CATALOG NUMBER: P3AS17R309835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1232.7
1°	1231.4
2°	1226.5
3°	1217.9
4°	1205.7
5°	1189.7
6°	1170.1
7°	1149.3
8°	1122.3
9°	1091.6
10°	1059.7
11°	1022.9
12°	983.7
13°	944.4
14°	901.5
15°	859.8
17.5°	750.6
20°	647.6
22.5°	551.9
25°	468.5
27.5°	392.5
30°	325.0
32.5°	262.5
35°	204.8
37.5°	157.0
40°	117.7
42.5°	85.9
45°	63.8
47.5°	47.8
50°	35.6
52.5°	28.2
55°	25.8
57.5°	22.1
60°	19.6
62.5°	15.9
65°	13.5
67.5°	12.3
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	3.7
82.5°	2.5
85°	2.5
87.5°	1.2



TEST NUMBER: P1276450
CATALOG NUMBER: P3AS17R309835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)