

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276480

Luminaire Tested: P3AS17R359835DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359835DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 951.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276480
CATALOG NUMBER: P3AS17R359835DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1276480
 CATALOG NUMBER: P3AS17R359835DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88	88	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	77	77	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68	68	68
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	60	60	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54	54	54
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49	49	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	44	44	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41	41	41
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	38	38	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	35	35	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	156106	156106	156106
5°	153180	152916	153180
10°	144019	143752	144019
15°	130398	130398	130670
20°	115417	115417	115417
25°	100361	100070	100070
30°	87026	86393	86697
35°	74900	74579	74900
40°	65008	64635	65008
45°	57091	56719	56719
50°	50659	50250	50250
55°	44577	44577	44577
60°	40392	39821	40392
65°	36320	36320	36320
70°	32249	32249	32249
75°	29145	28043	29145
80°	24751	24751	24751
85°	15347	15347	15347

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 57091 cd/sqm



TEST NUMBER: P1276480
 CATALOG NUMBER: P3AS17R359835DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.8	6.8
10°-20°	160.2	16.8
20°-30°	190.4	20.0
30°-40°	175.0	18.4
40°-50°	142.1	14.9
50°-60°	105.1	11.1
60°-70°	69.5	7.3
70°-80°	36.0	3.8
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.4	43.7
0°-40°	590.3	62.1
0°-60°	837.5	88.1
0°-90°	951.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	696	695	695	695	696	65
15°	574	574	574	574	576	160
25°	415	414	414	415	414	191
35°	280	279	279	280	280	175
45°	184	183	183	183	183	142
55°	117	117	117	117	117	106
65°	70	70	70	70	70	69
75°	34	34	33	34	34	36
85°	6	6	6	6	6	8
90°	0	0	0	0	0	



TEST NUMBER: P1276480

CATALOG NUMBER: P3AS17R359835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.9	711.9	711.9	711.9	711.9
1°	711.9	710.6	710.6	710.6	711.9
2°	709.4	709.4	709.4	709.4	709.4
3°	707.0	705.7	705.7	705.7	705.7
4°	702.0	700.8	700.8	700.8	700.8
5°	695.9	694.7	694.7	694.7	695.9
6°	688.5	687.3	686.1	686.1	687.3
7°	681.2	678.7	678.7	678.7	678.7
8°	670.1	668.9	668.9	668.9	668.9
9°	659.1	656.6	657.9	657.9	657.9
10°	646.8	645.6	645.6	645.6	646.8
11°	634.5	633.3	633.3	632.1	633.3
12°	619.8	619.8	619.8	619.8	619.8
13°	606.3	605.1	605.1	605.1	606.3
14°	591.6	590.4	590.4	590.4	590.4
15°	574.4	574.4	574.4	574.4	575.6
17.5°	535.1	533.9	535.1	535.1	536.3
20°	494.6	493.4	494.6	494.6	494.6
22.5°	454.1	454.1	452.9	454.1	455.3
25°	414.8	413.6	413.6	414.8	413.6
27.5°	378.0	376.8	376.8	376.8	376.8
30°	343.7	341.2	341.2	342.4	342.4
32.5°	308.1	308.1	309.3	308.1	308.1
35°	279.8	278.6	278.6	279.8	279.8
37.5°	251.6	250.4	250.4	251.6	251.6
40°	227.1	227.1	225.8	227.1	227.1
42.5°	203.7	203.7	203.7	203.7	203.7
45°	184.1	182.9	182.9	182.9	182.9
47.5°	164.5	164.5	164.5	163.2	164.5
50°	148.5	147.3	147.3	147.3	147.3
52.5°	131.3	131.3	131.3	131.3	131.3
55°	116.6	116.6	116.6	116.6	116.6
57.5°	104.3	103.1	103.1	103.1	103.1
60°	92.1	92.1	90.8	92.1	92.1
62.5°	79.8	79.8	79.8	79.8	79.8
65°	70.0	70.0	70.0	70.0	70.0
67.5°	60.1	60.1	60.1	60.1	60.1
70°	50.3	50.3	50.3	50.3	50.3
72.5°	43.0	41.7	41.7	41.7	41.7
75°	34.4	34.4	33.1	34.4	34.4
77.5°	25.8	25.8	25.8	25.8	25.8
80°	19.6	19.6	19.6	18.4	19.6
82.5°	12.3	12.3	12.3	12.3	12.3
85°	6.1	6.1	6.1	6.1	6.1
87.5°	1.2	1.2	1.2	2.5	2.5



TEST NUMBER: P1276480
CATALOG NUMBER: P3AS17R359835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)