

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281090

Luminaire Tested: P3AS05R20B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 412.1 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281090

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281090

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	91	90	89	88
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	91	90	89	88	87	86	85	84
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	90	89	88	87	86	85	84	83	82	81	80
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	86	85	84	83	82	81	80	79	78	77	76
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	82	81	80	79	78	77	76	75	74	73	72
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	80	79	78	77	76	75	74	73	72	71	70	69
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	75	74	73	72	71	70	69	68	67	66	65
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74	73	72	71	70	69	68	67	66	65	64	63
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	70	69	68	67	66	65	64	63	62	61	60
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	67	66	65	64	63	62	61	60	59	58	57
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	65	64	63	62	61	60	59	58	57	56	55

AVERAGE LUMINANCE (cd/sqm):

0°	316992
5°	288157
10°	212955
15°	131737
20°	75233
25°	42946
30°	24080
35°	13117
40°	7185
45°	3938
50°	2320
55°	1682
60°	1579
65°	1453
70°	1282
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3938 cd/sqm

TEST NUMBER: P1281090

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	27.5
10°-20°	161.8	39.3
20°-30°	84.5	20.5
30°-40°	32.7	7.9
40°-50°	10.6	2.6
50°-60°	4.2	1.0
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.6	87.3
0°-40°	392.3	95.2
0°-60°	407.1	98.8
0°-90°	412.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1446	
5°	1309	113
15°	580	162
25°	178	84
35°	49	33
45°	13	11
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1281090

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1445.6
1°	1442.8
2°	1425.7
3°	1399.4
4°	1358.8
5°	1309.1
6°	1250.2
7°	1184.9
8°	1109.3
9°	1035.6
10°	956.4
12.5°	760.2
15°	580.3
17.5°	434.2
20°	322.4
22.5°	238.8
25°	177.5
27.5°	130.9
30°	95.1
32.5°	68.9
35°	49.0
37.5°	35.4
40°	25.1
42.5°	17.9
45°	12.7
47.5°	9.2
50°	6.8
52.5°	5.2
55°	4.4
57.5°	4.0
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)