

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276511

Luminaire Tested: P3AS17R459835DE010 E3CB1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276511  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R459835DE010 E3CB1MB  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1645.1 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276511  
CATALOG NUMBER: P3AS17R459835DE010 E3CB1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1276511  
 CATALOG NUMBER: P3AS17R459835DE010 E3CB1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86			86
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	713188
5°	716991
10°	694977
15°	582387
20°	445192
25°	271008
30°	112777
35°	36138
40°	11250
45°	2295
50°	1672
55°	1873
60°	1623
65°	1920
70°	1603
75°	2118
80°	1515
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2295 cd/sqm



TEST NUMBER: P1276511  
 CATALOG NUMBER: P3AS17R459835DE010 E3CB1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.2	18.7
10°-20°	705.1	42.9
20°-30°	507.7	30.9
30°-40°	105.6	6.4
40°-50°	9.7	0.6
50°-60°	4.0	0.2
60°-70°	3.2	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1520.0	92.4
0°-40°	1625.6	98.8
0°-60°	1639.3	99.6
0°-90°	1645.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1645.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3252	
5°	3257	307
15°	2565	705
25°	1120	508
35°	135	106
45°	7	10
55°	5	4
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1276511  
CATALOG NUMBER: P3AS17R459835DE010 E3CB1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3252.4
2.5°	3253.7
5°	3257.3
7.5°	3234.0
10°	3121.2
12.5°	2885.6
15°	2565.4
17.5°	2237.8
20°	1907.8
22.5°	1528.7
25°	1120.1
27.5°	738.6
30°	445.4
32.5°	249.1
35°	135.0
37.5°	76.1
40°	39.3
42.5°	17.2
45°	7.4
47.5°	4.9
50°	4.9
52.5°	4.9
55°	4.9
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)