

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276526

Luminaire Tested: P3AS17R459835DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459835DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.1 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276526
CATALOG NUMBER: P3AS17R459835DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1276526
 CATALOG NUMBER: P3AS17R459835DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225596
5°	221593
10°	209682
15°	191238
20°	169111
25°	146863
30°	126045
35°	105042
40°	78261
45°	47912
50°	22174
55°	17357
60°	16665
65°	15255
70°	14169
75°	13471
80°	12375
85°	9309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 47912 cd/sqm



TEST NUMBER: P1276526
 CATALOG NUMBER: P3AS17R459835DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	8.8
10°-20°	234.5	22.0
20°-30°	278.7	26.2
30°-40°	242.1	22.8
40°-50°	121.4	11.4
50°-60°	42.2	4.0
60°-70°	29.6	2.8
70°-80°	16.5	1.6
80°-90°	5.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.2	57.1
0°-40°	849.4	79.8
0°-60°	1013.0	95.2
0°-90°	1064.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1029	
5°	1007	94
15°	842	235
25°	607	279
35°	392	242
45°	154	121
55°	45	42
65°	29	30
75°	16	16
85°	4	5
90°	0	



TEST NUMBER: P1276526
CATALOG NUMBER: P3AS17R459835DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1028.8
2.5°	1023.9
5°	1006.7
7.5°	979.7
10°	941.7
12.5°	895.1
15°	842.4
17.5°	783.5
20°	724.7
22.5°	664.6
25°	607.0
27.5°	551.8
30°	497.8
32.5°	446.3
35°	392.4
37.5°	334.8
40°	273.4
42.5°	213.4
45°	154.5
47.5°	101.8
50°	65.0
52.5°	50.3
55°	45.4
57.5°	41.7
60°	38.0
62.5°	34.3
65°	29.4
67.5°	25.8
70°	22.1
72.5°	18.4
75°	15.9
77.5°	12.3
80°	9.8
82.5°	7.4
85°	3.7
87.5°	2.5
90°	0.0

(END OF REPORT)