

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281131

Luminaire Tested: P3AS05R25B2750DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281131
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3CD1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 541.1 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281131

CATALOG NUMBER: P3AS05R25B2750DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281131

CATALOG NUMBER: P3AS05R25B2750DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	578397
5°	536450
10°	416024
15°	208605
20°	68536
25°	27244
30°	10229
35°	2971
40°	1345
45°	527
50°	443
55°	344
60°	395
65°	467
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 527 cd/sqm

TEST NUMBER: P1281131

CATALOG NUMBER: P3AS05R25B2750DE010 E3CD1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.4	39.6
10°-20°	255.7	47.3
20°-30°	57.7	10.7
30°-40°	9.4	1.7
40°-50°	1.7	0.3
50°-60°	0.9	0.2
60°-70°	0.8	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.8	97.5
0°-40°	537.1	99.3
0°-60°	539.8	99.8
0°-90°	541.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	541.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2638	
5°	2437	214
15°	919	256
25°	113	58
35°	11	9
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281131

CATALOG NUMBER: P3AS05R25B2750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2637.7
1°	2633.5
2°	2612.2
3°	2573.1
4°	2514.1
5°	2437.1
6°	2345.3
7°	2245.9
8°	2132.0
9°	2007.4
10°	1868.4
11°	1708.2
12°	1523.7
13°	1330.8
14°	1123.8
15°	918.9
17.5°	523.6
20°	293.7
22.5°	177.2
25°	112.6
27.5°	69.3
30°	40.4
32.5°	21.3
35°	11.1
37.5°	7.2
40°	4.7
42.5°	3.0
45°	1.7
47.5°	1.3
50°	1.3
52.5°	1.3
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1281131

CATALOG NUMBER: P3AS05R25B2750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)