

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281155

Luminaire Tested: P3AS05R25B2750DE010 E3D1WH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3D1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281155

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281155

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	589207
5°	545827
10°	422303
15°	201704
20°	66506
25°	28042
30°	10862
35°	4711
40°	1574
45°	713
50°	273
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1281155

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.0	40.5
10°-20°	247.9	46.1
20°-30°	57.6	10.7
30°-40°	12.1	2.2
40°-50°	2.0	0.4
50°-60°	0.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.5	97.3
0°-40°	535.6	99.5
0°-60°	537.9	100.0
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2687	
5°	2480	218
15°	888	248
25°	116	58
35°	18	12
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281155

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2687.0
1°	2681.6
2°	2653.7
3°	2614.5
4°	2554.6
5°	2479.7
6°	2383.5
7°	2282.8
8°	2169.9
9°	2042.5
10°	1896.6
11°	1727.5
12°	1533.4
13°	1320.8
14°	1098.4
15°	888.5
16°	702.8
17°	547.5
18°	430.7
19°	344.5
20°	285.0
21°	238.2
22°	199.9
23°	167.0
24°	139.7
25°	115.9
27.5°	68.7
30°	42.9
32.5°	27.5
35°	17.6
37.5°	10.5
40°	5.5
42.5°	3.5
45°	2.3
47.5°	1.4
50°	0.8
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0



TEST NUMBER: P1281155

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)