

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281163

Luminaire Tested: P3AS05R25B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 201.0 lumens
Efficiency: N/A
Efficacy: 34.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281163

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281163

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90		
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86		
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82		
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78		
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75		
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66		
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128937
5°	120295
10°	96369
15°	65403
20°	39577
25°	23155
30°	13192
35°	7254
40°	3836
45°	2016
50°	1194
55°	879
60°	746
65°	778
70°	769
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2016 cd/sqm

TEST NUMBER: P1281163

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	24.1
10°-20°	79.2	39.4
20°-30°	45.3	22.5
30°-40°	17.9	8.9
40°-50°	5.5	2.7
50°-60°	2.2	1.1
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.0	86.1
0°-40°	190.8	94.9
0°-60°	198.5	98.7
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	588	
5°	546	48
15°	288	79
25°	96	45
35°	27	18
45°	6	5
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281163

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	588.0
1°	586.8
2°	582.0
3°	573.6
4°	561.9
5°	546.5
6°	528.4
7°	508.1
8°	484.4
9°	460.2
10°	432.8
11°	405.7
12°	375.9
13°	346.5
14°	316.4
15°	288.1
17.5°	223.4
20°	169.6
22.5°	127.4
25°	95.7
27.5°	70.9
30°	52.1
32.5°	37.6
35°	27.1
37.5°	19.2
40°	13.4
42.5°	9.2
45°	6.5
47.5°	4.6
50°	3.5
52.5°	2.7
55°	2.3
57.5°	2.1
60°	1.7
62.5°	1.5
65°	1.5
67.5°	1.3
70°	1.2
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1281163

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)