

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281196

Luminaire Tested: P3AS05R25B2750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 167.0 lumens
Efficiency: N/A
Efficacy: 28.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281196

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281196

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39690
5°	38741
10°	35893
15°	31964
20°	27489
25°	23348
30°	19218
35°	14991
40°	10792
45°	6853
50°	4060
55°	2791
60°	2544
65°	2387
70°	2116
75°	1949
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6853 cd/sqm

TEST NUMBER: P1281196

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	9.8
10°-20°	39.1	23.4
20°-30°	44.2	26.4
30°-40°	35.0	20.9
40°-50°	17.7	10.6
50°-60°	7.1	4.2
60°-70°	4.5	2.7
70°-80°	2.5	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	99.6	59.6
0°-40°	134.5	80.6
0°-60°	159.3	95.4
0°-90°	167.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	167.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	181	
5°	176	16
15°	141	39
25°	96	44
35°	56	35
45°	22	18
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1281196

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	181.0
1°	181.0
2°	180.4
3°	179.3
4°	177.9
5°	176.0
6°	173.7
7°	171.0
8°	168.1
9°	164.8
10°	161.2
11°	157.3
12°	153.5
13°	149.2
14°	145.0
15°	140.8
17.5°	129.2
20°	117.8
22.5°	106.9
25°	96.5
27.5°	86.3
30°	75.9
32.5°	66.2
35°	56.0
37.5°	46.6
40°	37.7
42.5°	29.3
45°	22.1
47.5°	16.4
50°	11.9
52.5°	8.9
55°	7.3
57.5°	6.7
60°	5.8
62.5°	5.2
65°	4.6
67.5°	4.0
70°	3.3
72.5°	2.9
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1281196

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)