

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281211

Luminaire Tested: P3AS05R25B2750DE010 E3DLD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DLD1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 341.0 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281211

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281211

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81046
5°	79111
10°	73301
15°	65290
20°	56098
25°	47688
30°	39272
35°	30597
40°	22013
45°	13955
50°	8256
55°	5696
60°	5219
65°	4825
70°	4360
75°	3982
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13955 cd/sqm

TEST NUMBER: P1281211

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	9.8
10°-20°	79.8	23.4
20°-30°	90.2	26.5
30°-40°	71.4	20.9
40°-50°	36.0	10.6
50°-60°	14.4	4.2
60°-70°	9.2	2.7
70°-80°	5.1	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.4	59.6
0°-40°	274.8	80.6
0°-60°	325.2	95.4
0°-90°	341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	370	
5°	359	33
15°	288	80
25°	197	90
35°	114	71
45°	45	36
55°	15	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1281211

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	369.6
1°	369.6
2°	368.3
3°	366.2
4°	363.2
5°	359.4
6°	354.7
7°	349.2
8°	343.2
9°	336.5
10°	329.2
11°	321.2
12°	313.5
13°	304.6
14°	296.1
15°	287.6
17.5°	263.8
20°	240.4
22.5°	218.4
25°	197.1
27.5°	176.3
30°	155.1
32.5°	135.1
35°	114.3
37.5°	95.2
40°	76.9
42.5°	59.9
45°	45.0
47.5°	33.6
50°	24.2
52.5°	18.3
55°	14.9
57.5°	13.6
60°	11.9
62.5°	10.6
65°	9.3
67.5°	8.1
70°	6.8
72.5°	5.9
75°	4.7
77.5°	3.8
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.4



TEST NUMBER: P1281211

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)