

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276573

Luminaire Tested: P3AS17R559835DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559835DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1632.1 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276573
CATALOG NUMBER: P3AS17R559835DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1276573
 CATALOG NUMBER: P3AS17R559835DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452639
5°	448425
10°	466458
15°	459980
20°	424167
25°	345117
30°	209627
35°	72571
40°	20725
45°	9892
50°	4196
55°	1873
60°	2149
65°	1920
70°	1603
75°	2118
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9892 cd/sqm



TEST NUMBER: P1276573
 CATALOG NUMBER: P3AS17R559835DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.9	12.1
10°-20°	563.1	34.5
20°-30°	627.8	38.5
30°-40°	205.4	12.6
40°-50°	27.1	1.7
50°-60°	5.7	0.4
60°-70°	3.4	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.9	85.0
0°-40°	1593.3	97.6
0°-60°	1626.1	99.6
0°-90°	1632.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1632.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2064	
5°	2037	197
15°	2026	563
25°	1426	628
35°	271	205
45°	32	27
55°	5	6
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1276573
CATALOG NUMBER: P3AS17R559835DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2064.2
2.5°	2049.5
5°	2037.2
7.5°	2066.7
10°	2094.9
12.5°	2080.2
15°	2026.2
17.5°	1940.3
20°	1817.7
22.5°	1648.4
25°	1426.4
27.5°	1144.3
30°	827.9
32.5°	507.8
35°	271.1
37.5°	137.4
40°	72.4
42.5°	46.6
45°	31.9
47.5°	22.1
50°	12.3
52.5°	7.4
55°	4.9
57.5°	4.9
60°	4.9
62.5°	3.7
65°	3.7
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)