

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281217

Luminaire Tested: P3AS05R25B2750DE010 E3DLD1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DLD1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 319.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281217

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1281217

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75805
5°	74004
10°	68580
15°	61067
20°	52481
25°	44615
30°	36740
35°	28616
40°	20581
45°	13056
50°	7744
55°	5314
60°	4868
65°	4514
70°	4103
75°	3728
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13056 cd/sqm

TEST NUMBER: P1281217

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.2	9.8
10°-20°	74.7	23.4
20°-30°	84.4	26.5
30°-40°	66.8	20.9
40°-50°	33.7	10.6
50°-60°	13.5	4.2
60°-70°	8.6	2.7
70°-80°	4.8	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.3	59.6
0°-40°	257.0	80.6
0°-60°	304.2	95.4
0°-90°	319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	346	
5°	336	31
15°	269	75
25°	184	84
35°	107	67
45°	42	34
55°	14	14
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1281217

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	345.7
1°	345.7
2°	344.6
3°	342.6
4°	339.8
5°	336.2
6°	331.8
7°	326.7
8°	321.1
9°	314.7
10°	308.0
11°	300.4
12°	293.3
13°	284.9
14°	277.0
15°	269.0
17.5°	246.8
20°	224.9
22.5°	204.3
25°	184.4
27.5°	164.9
30°	145.1
32.5°	126.4
35°	106.9
37.5°	89.0
40°	71.9
42.5°	56.0
45°	42.1
47.5°	31.4
50°	22.7
52.5°	17.1
55°	13.9
57.5°	12.7
60°	11.1
62.5°	9.9
65°	8.7
67.5°	7.6
70°	6.4
72.5°	5.6
75°	4.4
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.4



TEST NUMBER: P1281217

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLD1WMH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)