

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281236

Luminaire Tested: P3AS05R25B2750DE010 E3DLP1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DLP1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 46.3 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281236

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1LI_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281236

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82	79	76	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63	62
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64	59	56	55
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99115
5°	95091
10°	83298
15°	66947
20°	51454
25°	38930
30°	28131
35°	18685
40°	11336
45°	6605
50°	4196
55°	3403
60°	2982
65°	2646
70°	2180
75°	2203
80°	1642
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6605 cd/sqm

TEST NUMBER: P1281236

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	14.4
10°-20°	81.6	29.9
20°-30°	73.8	27.0
30°-40°	44.3	16.2
40°-50°	17.6	6.4
50°-60°	8.1	3.0
60°-70°	4.9	1.8
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.6	71.3
0°-40°	239.0	87.5
0°-60°	264.7	96.9
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	432	39
15°	295	82
25°	161	74
35°	70	44
45°	21	18
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1281236

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	452.0
1°	452.0
2°	449.9
3°	445.2
4°	439.2
5°	432.0
6°	422.6
7°	412.0
8°	399.6
9°	387.3
10°	374.1
11°	358.8
12°	343.0
13°	327.3
14°	311.5
15°	294.9
17.5°	255.8
20°	220.5
22.5°	188.5
25°	160.9
27.5°	134.9
30°	111.1
32.5°	89.4
35°	69.8
37.5°	53.2
40°	39.6
42.5°	28.9
45°	21.3
47.5°	16.2
50°	12.3
52.5°	10.2
55°	8.9
57.5°	7.7
60°	6.8
62.5°	5.5
65°	5.1
67.5°	4.3
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1281236

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)