

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281248

Luminaire Tested: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1281248  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R25B2750DE010 E3DLP1WMH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 251.0 lumens  
Efficiency: N/A  
Efficacy: 42.5 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281248

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1281248

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  | 96  | 95  | 93  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  | 90  | 88  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  | 80  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  | 79  | 76  | 75  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  |  | 79  | 75  | 72  |  | 78  | 74  | 71  | 70  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  | 70  | 67  | 66  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  | 66  | 63  | 62  |
| 8   | 80  | 70  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  | 63  | 60  | 58  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 61  | 57  | 65  | 60  | 57  |  | 65  | 60  | 57  |  | 64  | 59  | 56  | 55  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  | 57  | 54  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 91133 |
| 5°  | 87431 |
| 10° | 76596 |
| 15° | 61567 |
| 20° | 47301 |
| 25° | 35784 |
| 30° | 25852 |
| 35° | 17186 |
| 40° | 10420 |
| 45° | 6078  |
| 50° | 3855  |
| 55° | 3135  |
| 60° | 2763  |
| 65° | 2439  |
| 70° | 1988  |
| 75° | 1949  |
| 80° | 1515  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 6078 cd/sqm

TEST NUMBER: P1281248

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 36.2   | 14.4      |
| 10°-20°   | 75.0   | 29.9      |
| 20°-30°   | 67.8   | 27.0      |
| 30°-40°   | 40.7   | 16.2      |
| 40°-50°   | 16.2   | 6.4       |
| 50°-60°   | 7.4    | 3.0       |
| 60°-70°   | 4.5    | 1.8       |
| 70°-80°   | 2.4    | 1.0       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 179.0  | 71.3      |
| 0°-40°    | 219.7  | 87.5      |
| 0°-60°    | 243.3  | 96.9      |
| 0°-90°    | 251.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 251.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 416 |      |
| 5°  | 397 | 36   |
| 15° | 271 | 75   |
| 25° | 148 | 68   |
| 35° | 64  | 41   |
| 45° | 20  | 16   |
| 55° | 8   | 7    |
| 65° | 5   | 5    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1281248

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 415.6 |
| 1°    | 415.6 |
| 2°    | 413.6 |
| 3°    | 409.3 |
| 4°    | 403.8 |
| 5°    | 397.2 |
| 6°    | 388.6 |
| 7°    | 378.8 |
| 8°    | 367.4 |
| 9°    | 356.1 |
| 10°   | 344.0 |
| 11°   | 329.9 |
| 12°   | 315.4 |
| 13°   | 300.9 |
| 14°   | 286.4 |
| 15°   | 271.2 |
| 17.5° | 235.2 |
| 20°   | 202.7 |
| 22.5° | 173.4 |
| 25°   | 147.9 |
| 27.5° | 124.0 |
| 30°   | 102.1 |
| 32.5° | 82.2  |
| 35°   | 64.2  |
| 37.5° | 48.9  |
| 40°   | 36.4  |
| 42.5° | 26.6  |
| 45°   | 19.6  |
| 47.5° | 14.9  |
| 50°   | 11.3  |
| 52.5° | 9.4   |
| 55°   | 8.2   |
| 57.5° | 7.0   |
| 60°   | 6.3   |
| 62.5° | 5.1   |
| 65°   | 4.7   |
| 67.5° | 3.9   |
| 70°   | 3.1   |
| 72.5° | 2.7   |
| 75°   | 2.3   |
| 77.5° | 2.0   |
| 80°   | 1.2   |
| 82.5° | 0.8   |
| 85°   | 0.8   |
| 87.5° | 0.4   |



TEST NUMBER: P1281248

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1WMH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)