

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276616

Luminaire Tested: P3AS17R609835DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609835DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1011.0 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276616

CATALOG NUMBER: P3AS17R609835DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1276616

CATALOG NUMBER: P3AS17R609835DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179459
5°	177459
10°	171317
15°	161840
20°	149183
25°	135080
30°	119917
35°	102473
40°	81496
45°	57463
50°	34319
55°	17357
60°	16665
65°	15255
70°	14169
75°	13556
80°	12375
85°	9309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57463 cd/sqm

TEST NUMBER: P1276616

CATALOG NUMBER: P3AS17R609835DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	7.5
10°-20°	199.2	19.7
20°-30°	255.8	25.3
30°-40°	237.2	23.5
40°-50°	144.4	14.3
50°-60°	48.1	4.8
60°-70°	29.3	2.9
70°-80°	16.5	1.6
80°-90°	4.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.8	52.5
0°-40°	768.0	76.0
0°-60°	960.5	95.0
0°-90°	1011.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1011.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	818	
5°	806	76
15°	713	199
25°	558	256
35°	383	237
45°	185	144
55°	45	48
65°	29	29
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1276616

CATALOG NUMBER: P3AS17R609835DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	818.4
2.5°	814.8
5°	806.2
7.5°	790.2
10°	769.4
12.5°	743.6
15°	712.9
17.5°	677.3
20°	639.3
22.5°	598.8
25°	558.3
27.5°	516.6
30°	473.6
32.5°	430.7
35°	382.8
37.5°	332.5
40°	284.7
42.5°	234.4
45°	185.3
47.5°	143.6
50°	100.6
52.5°	60.1
55°	45.4
57.5°	41.7
60°	38.0
62.5°	33.1
65°	29.4
67.5°	25.8
70°	22.1
72.5°	18.4
75°	16.0
77.5°	12.3
80°	9.8
82.5°	6.1
85°	3.7
87.5°	2.5
90°	0.0

(END OF REPORT)