

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281271

Luminaire Tested: P3AS05R30B2750DE010 E3CB1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3CB1MB_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 540.9 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281271
CATALOG NUMBER: P3AS05R30B2750DE010 E3CB1MB_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281271

CATALOG NUMBER: P3AS05R30B2750DE010 E3CB1MB_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	92	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	78	75	80	78	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440557
5°	432224
10°	382625
15°	242430
20°	92011
25°	27244
30°	10761
35°	3293
40°	1460
45°	527
50°	443
55°	306
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 527 cd/sqm



TEST NUMBER: P1281271
 CATALOG NUMBER: P3AS05R30B2750DE010 E3CB1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.5	33.4
10°-20°	281.3	52.0
20°-30°	65.3	12.1
30°-40°	10.1	1.9
40°-50°	1.7	0.3
50°-60°	0.8	0.1
60°-70°	0.6	0.1
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.2	97.5
0°-40°	537.3	99.3
0°-60°	539.8	99.8
0°-90°	540.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2009	
5°	1964	181
15°	1068	281
25°	113	65
35°	12	10
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1281271
CATALOG NUMBER: P3AS05R30B2750DE010 E3CB1MB_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2009.1
1°	2007.8
2°	2002.3
3°	1992.9
4°	1981.1
5°	1963.6
6°	1942.0
7°	1909.7
8°	1865.5
9°	1800.5
10°	1718.4
11°	1612.6
12°	1493.2
13°	1360.6
14°	1214.9
15°	1067.9
17.5°	698.6
20°	394.3
22.5°	201.4
25°	112.6
27.5°	69.3
30°	42.5
32.5°	22.9
35°	12.3
37.5°	8.1
40°	5.1
42.5°	3.0
45°	1.7
47.5°	1.3
50°	1.3
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1281271
CATALOG NUMBER: P3AS05R30B2750DE010 E3CB1MB_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)