

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281303

Luminaire Tested: P3AS05R30B2750DE010 E3D1LI_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3D1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 494.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281303

CATALOG NUMBER: P3AS05R30B2750DE010 E3D1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281303

CATALOG NUMBER: P3AS05R30B2750DE010 E3D1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	87	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	84	83	82
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	81	80	79
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	79	78	77
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	77	76	75
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	75	74	73
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393039
5°	387914
10°	338693
15°	215279
20°	85291
25°	28477
30°	13268
35°	5996
40°	2319
45°	1116
50°	341
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1116 cd/sqm

TEST NUMBER: P1281303

CATALOG NUMBER: P3AS05R30B2750DE010 E3D1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.1	32.6
10°-20°	249.9	50.6
20°-30°	64.4	13.0
30°-40°	15.1	3.1
40°-50°	3.0	0.6
50°-60°	0.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.4	96.2
0°-40°	490.5	99.3
0°-60°	493.9	100.0
0°-90°	494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	494.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1792	
5°	1762	161
15°	948	250
25°	118	64
35°	22	15
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281303

CATALOG NUMBER: P3AS05R30B2750DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1792.4
1°	1791.1
2°	1786.9
3°	1782.1
4°	1775.0
5°	1762.3
6°	1741.8
7°	1707.7
8°	1661.1
9°	1600.3
10°	1521.1
11°	1426.9
12°	1324.1
13°	1205.8
14°	1081.9
15°	948.3
16°	817.3
17°	691.1
18°	570.1
19°	459.1
20°	365.5
21°	287.6
22°	226.3
23°	179.1
24°	143.4
25°	117.7
26°	98.2
27°	83.4
28°	72.1
29°	61.7
30°	52.4
32.5°	33.0
35°	22.4
37.5°	14.0
40°	8.1
42.5°	5.4
45°	3.6
47.5°	2.1
50°	1.0
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2



TEST NUMBER: P1281303

CATALOG NUMBER: P3AS05R30B2750DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)