

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276650

Luminaire Tested: P3AS17R659835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1230.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276650
CATALOG NUMBER: P3AS17R659835DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276650
 CATALOG NUMBER: P3AS17R659835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290064
5°	286594
10°	275702
15°	258276
20°	232304
25°	197261
30°	154277
35°	109941
40°	71935
45°	44470
50°	22583
55°	7952
60°	6973
65°	7005
70°	6283
75°	6270
80°	6188
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 44470 cd/sqm



TEST NUMBER: P1276650
 CATALOG NUMBER: P3AS17R659835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	9.9
10°-20°	316.6	25.7
20°-30°	370.0	30.1
30°-40°	258.6	21.0
40°-50°	113.8	9.3
50°-60°	25.3	2.1
60°-70°	12.9	1.0
70°-80°	7.8	0.6
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.9	65.8
0°-40°	1067.5	86.8
0°-60°	1206.6	98.1
0°-90°	1230.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1230.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1323	
5°	1302	122
15°	1138	317
25°	815	370
35°	411	259
45°	143	114
55°	21	25
65°	14	13
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1276650
CATALOG NUMBER: P3AS17R659835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1322.8
2.5°	1317.9
5°	1302.0
7.5°	1275.0
10°	1238.2
12.5°	1192.9
15°	1137.7
17.5°	1070.3
20°	995.5
22.5°	910.9
25°	815.3
27.5°	714.7
30°	609.3
32.5°	507.6
35°	410.7
37.5°	326.1
40°	251.3
42.5°	190.0
45°	143.4
47.5°	105.4
50°	66.2
52.5°	34.3
55°	20.8
57.5°	18.4
60°	15.9
62.5°	14.7
65°	13.5
67.5°	11.0
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	4.9
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

(END OF REPORT)