

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281386

Luminaire Tested: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1281386  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R30B2750DE010 E3DLP1GPH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 134.0 lumens  
Efficiency: N/A  
Efficacy: 22.7 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281386

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1281386

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  | 96  | 95  |  | 93  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  | 90  | 88  |  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  |  | 80  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  | 79  | 76  |  | 74  |
| 5   | 92  | 84  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 78  | 74  | 71  |  | 70  |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  | 70  | 67  |  | 65  |
| 7   | 83  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 63  |  | 71  | 67  | 63  |  | 70  | 66  | 63  |  | 61  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 68  | 63  | 60  |  | 67  | 62  | 59  |  | 58  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  |  | 64  | 60  | 56  |  | 63  | 59  | 56  |  | 55  |
| 10  | 73  | 63  | 58  | 54  | 72  | 63  | 57  | 54  | 62  | 57  | 54  |  | 61  | 57  | 53  |  | 61  | 56  | 53  |  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 45786 |
| 5°  | 44354 |
| 10° | 39968 |
| 15° | 33076 |
| 20° | 25599 |
| 25° | 19211 |
| 30° | 13952 |
| 35° | 9289  |
| 40° | 5696  |
| 45° | 3349  |
| 50° | 2047  |
| 55° | 1682  |
| 60° | 1447  |
| 65° | 1193  |
| 70° | 1090  |
| 75° | 1017  |
| 80° | 758   |
| 85° | 1006  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3349 cd/sqm

TEST NUMBER: P1281386

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 18.5   | 13.8      |
| 10°-20°   | 40.1   | 29.9      |
| 20°-30°   | 36.5   | 27.2      |
| 30°-40°   | 22.1   | 16.5      |
| 40°-50°   | 8.8    | 6.6       |
| 50°-60°   | 3.9    | 2.9       |
| 60°-70°   | 2.4    | 1.8       |
| 70°-80°   | 1.3    | 1.0       |
| 80°-90°   | 0.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 95.2   | 71.0      |
| 0°-40°    | 117.2  | 87.5      |
| 0°-60°    | 130.0  | 97.0      |
| 0°-90°    | 134.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 134.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 209 |      |
| 5°  | 202 | 19   |
| 15° | 146 | 40   |
| 25° | 79  | 37   |
| 35° | 35  | 22   |
| 45° | 11  | 9    |
| 55° | 4   | 4    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1281386

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 208.8 |
| 1°    | 208.6 |
| 2°    | 207.8 |
| 3°    | 206.3 |
| 4°    | 204.2 |
| 5°    | 201.5 |
| 6°    | 198.2 |
| 7°    | 194.7 |
| 8°    | 190.1 |
| 9°    | 184.9 |
| 10°   | 179.5 |
| 11°   | 173.3 |
| 12°   | 166.6 |
| 13°   | 160.0 |
| 14°   | 152.7 |
| 15°   | 145.7 |
| 17.5° | 127.2 |
| 20°   | 109.7 |
| 22.5° | 93.5  |
| 25°   | 79.4  |
| 27.5° | 66.5  |
| 30°   | 55.1  |
| 32.5° | 44.5  |
| 35°   | 34.7  |
| 37.5° | 26.6  |
| 40°   | 19.9  |
| 42.5° | 14.5  |
| 45°   | 10.8  |
| 47.5° | 8.1   |
| 50°   | 6.0   |
| 52.5° | 4.8   |
| 55°   | 4.4   |
| 57.5° | 3.7   |
| 60°   | 3.3   |
| 62.5° | 2.7   |
| 65°   | 2.3   |
| 67.5° | 2.1   |
| 70°   | 1.7   |
| 72.5° | 1.5   |
| 75°   | 1.2   |
| 77.5° | 1.0   |
| 80°   | 0.6   |
| 82.5° | 0.4   |
| 85°   | 0.4   |
| 87.5° | 0.2   |



TEST NUMBER: P1281386

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1GPH\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)