

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281393

Luminaire Tested: P3AS05R30B2750DE010 E3DLP1LI\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1281393  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R30B2750DE010 E3DLP1LI\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 252.0 lumens  
Efficiency: N/A  
Efficacy: 42.7 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281393  
CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1LI\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1281393  
 CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86112
5°	83425
10°	75171
15°	62180
20°	48141
25°	36123
30°	26207
35°	17480
40°	10734
45°	6295
50°	3855
55°	3135
60°	2763
65°	2231
70°	1988
75°	1949
80°	1515
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6295 cd/sqm



TEST NUMBER: P1281393  
 CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.9	13.8
10°-20°	75.4	29.9
20°-30°	68.6	27.2
30°-40°	41.5	16.5
40°-50°	16.6	6.6
50°-60°	7.4	2.9
60°-70°	4.4	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	178.9	71.0
0°-40°	220.4	87.5
0°-60°	244.4	97.0
0°-90°	252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	252.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	393	
5°	379	35
15°	274	75
25°	149	69
35°	65	41
45°	20	17
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1281393  
CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	392.7
1°	392.3
2°	390.8
3°	388.0
4°	384.1
5°	379.0
6°	372.8
7°	366.1
8°	357.5
9°	347.8
10°	337.6
11°	325.9
12°	313.4
13°	300.9
14°	287.2
15°	273.9
17.5°	239.1
20°	206.3
22.5°	175.8
25°	149.3
27.5°	125.0
30°	103.5
32.5°	83.6
35°	65.3
37.5°	50.0
40°	37.5
42.5°	27.4
45°	20.3
47.5°	15.2
50°	11.3
52.5°	9.0
55°	8.2
57.5°	7.0
60°	6.3
62.5°	5.1
65°	4.3
67.5°	3.9
70°	3.1
72.5°	2.7
75°	2.3
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1281393  
CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1LI\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)