

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281403

Luminaire Tested: P3AS05R30B2750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 414.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281403

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281403

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	99	100	101	102	103	104	105	106	107	108
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	93	95	97	99	101	103	105	107	109	111	113
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	89	91	93	95	97	99	101	103	105	107	109
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	85	88	90	92	94	96	98	100	102	104	106
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	81	84	86	88	90	92	94	96	98	100	102
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	76	78	81	83	85	87	89	91	93	95	97	99
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	73	75	79	81	83	85	87	89	91	93	95	97
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	70	72	76	78	80	82	84	86	88	90	92	94
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	67	69	73	75	77	79	81	83	85	87	89	91
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	67	71	73	75	77	79	81	83	85	87	89

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241582
5°	229936
10°	193405
15°	139479
20°	86528
25°	49213
30°	27321
35°	14857
40°	7843
45°	4249
50°	2252
55°	1491
60°	1360
65°	1401
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4249 cd/sqm

TEST NUMBER: P1281403

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	22.7
10°-20°	167.2	40.4
20°-30°	96.6	23.3
30°-40°	36.7	8.9
40°-50°	11.3	2.7
50°-60°	3.8	0.9
60°-70°	2.5	0.6
70°-80°	1.4	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.9	86.4
0°-40°	394.6	95.3
0°-60°	409.6	98.9
0°-90°	414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1102	
5°	1045	94
15°	614	167
25°	203	97
35°	56	37
45°	14	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281403

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1101.7
1°	1100.9
2°	1094.3
3°	1081.8
4°	1066.1
5°	1044.6
6°	1017.2
7°	986.7
8°	952.7
9°	912.0
10°	868.6
11°	821.7
12°	772.0
13°	720.0
14°	667.2
15°	614.4
17.5°	484.6
20°	370.8
22.5°	274.9
25°	203.4
27.5°	147.8
30°	107.9
32.5°	77.8
35°	55.5
37.5°	38.7
40°	27.4
42.5°	19.2
45°	13.7
47.5°	9.4
50°	6.6
52.5°	4.7
55°	3.9
57.5°	3.5
60°	3.1
62.5°	2.7
65°	2.7
67.5°	2.3
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1281403

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)