

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281405

Luminaire Tested: P3AS05R30B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 422.0 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281405

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281405

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	90	86	82	78	75	71	69
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	90	86	82	78	75	71	69	66	63	60	57
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	86	82	78	75	71	69	66	63	60	57	54
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	82	78	75	71	69	66	63	60	57	54	51
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	78	75	71	69	66	63	60	57	54	51	48
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	74	71	69	66	63	60	57	54	51	48	45
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	71	69	66	63	60	57	54	51	48	45	42
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	72	69	66	63	60	57	54	51	48	45	42	39
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	66	63	60	57	54	51	48	45	42	39	36
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	63	60	57	54	51	48	45	42	39	36	33
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	61	58	55	52	49	46	43	40	37	34	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246252
5°	234382
10°	197146
15°	142180
20°	88184
25°	50156
30°	27852
35°	15151
40°	7986
45°	4342
50°	2320
55°	1529
60°	1403
65°	1453
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4342 cd/sqm

TEST NUMBER: P1281405

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.9	22.7
10°-20°	170.4	40.4
20°-30°	98.5	23.3
30°-40°	37.4	8.9
40°-50°	11.5	2.7
50°-60°	3.9	0.9
60°-70°	2.6	0.6
70°-80°	1.4	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.8	86.4
0°-40°	402.2	95.3
0°-60°	417.5	98.9
0°-90°	422.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	422.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1123	
5°	1065	96
15°	626	170
25°	207	98
35°	57	37
45°	14	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281405

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1123.0
1°	1122.2
2°	1115.4
3°	1102.7
4°	1086.7
5°	1064.8
6°	1036.9
7°	1005.8
8°	971.1
9°	929.6
10°	885.4
11°	837.6
12°	786.9
13°	733.9
14°	680.1
15°	626.3
17.5°	493.9
20°	377.9
22.5°	280.2
25°	207.3
27.5°	150.7
30°	110.0
32.5°	79.3
35°	56.6
37.5°	39.5
40°	27.9
42.5°	19.5
45°	14.0
47.5°	9.6
50°	6.8
52.5°	4.8
55°	4.0
57.5°	3.6
60°	3.2
62.5°	2.8
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1281405

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)