

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276821

Luminaire Tested: P3AS20R359835D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359835D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1034.0 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276821

CATALOG NUMBER: P3AS20R359835D010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1276821

CATALOG NUMBER: P3AS20R359835D010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332364
5°	324168
10°	296365
15°	251556
20°	199144
25°	150614
30°	109637
35°	74151
40°	45571
45°	26173
50°	15761
55°	12769
60°	11183
65°	9910
70°	8142
75°	8133
80°	8082
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26173 cd/sqm

TEST NUMBER: P1276821

CATALOG NUMBER: P3AS20R359835D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	13.2
10°-20°	305.5	29.5
20°-30°	285.8	27.6
30°-40°	174.9	16.9
40°-50°	68.9	6.7
50°-60°	30.4	2.9
60°-70°	18.9	1.8
70°-80°	10.1	1.0
80°-90°	3.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.4	70.3
0°-40°	902.3	87.3
0°-60°	1001.6	96.9
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1516	
5°	1473	136
15°	1108	305
25°	622	286
35°	277	175
45°	84	69
55°	33	30
65°	19	19
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1276821

CATALOG NUMBER: P3AS20R359835D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1515.7
1°	1517.3
2°	1512.5
3°	1502.9
4°	1488.6
5°	1472.7
6°	1452.0
7°	1428.1
8°	1399.4
9°	1367.6
10°	1331.0
11°	1292.8
12°	1251.4
13°	1206.8
14°	1157.4
15°	1108.1
17.5°	980.7
20°	853.4
22.5°	730.8
25°	622.5
27.5°	522.2
30°	433.0
32.5°	350.3
35°	277.0
37.5°	211.7
40°	159.2
42.5°	114.6
45°	84.4
47.5°	60.5
50°	46.2
52.5°	38.2
55°	33.4
57.5°	28.7
60°	25.5
62.5°	22.3
65°	19.1
67.5°	15.9
70°	12.7
72.5°	11.1
75°	9.6
77.5°	8.0
80°	6.4
82.5°	4.8
85°	3.2
87.5°	1.6



TEST NUMBER: P1276821

CATALOG NUMBER: P3AS20R359835D010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)