

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281470

Luminaire Tested: P3AS05R35B2750DE010 E3DL1H_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3DL1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 418.1 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281470
CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281470
 CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210816
5°	202619
10°	176528
15°	135211
20°	90471
25°	54729
30°	31423
35°	17561
40°	9332
45°	4807
50°	2320
55°	1835
60°	1754
65°	1453
70°	1539
75°	1356
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4807 cd/sqm



TEST NUMBER: P1281470
 CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	20.0
10°-20°	162.3	38.8
20°-30°	106.3	25.4
30°-40°	43.1	10.3
40°-50°	12.9	3.1
50°-60°	4.4	1.1
60°-70°	3.0	0.7
70°-80°	1.7	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.3	84.3
0°-40°	395.4	94.6
0°-60°	412.8	98.7
0°-90°	418.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	418.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	961	
5°	920	84
15°	596	162
25°	226	106
35°	66	43
45°	16	13
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1281470
CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	961.4
1°	959.8
2°	955.5
3°	946.7
4°	936.4
5°	920.5
6°	900.6
7°	878.3
8°	853.3
9°	824.6
10°	792.8
11°	757.4
12°	720.5
13°	679.1
14°	639.8
15°	595.6
17.5°	488.7
20°	387.7
22.5°	298.2
25°	226.2
27.5°	168.6
30°	124.1
32.5°	91.1
35°	65.6
37.5°	46.5
40°	32.6
42.5°	22.7
45°	15.5
47.5°	10.3
50°	6.8
52.5°	5.2
55°	4.8
57.5°	4.4
60°	4.0
62.5°	3.6
65°	2.8
67.5°	2.4
70°	2.4
72.5°	2.0
75°	1.6
77.5°	1.2
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1281470
CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1H_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)