

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281512

Luminaire Tested: P3AS05R35B2750DE010 E3DLD1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3DLD1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 321.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281512
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281512
 CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73327
5°	71781
10°	67222
15°	60341
20°	52481
25°	44712
30°	37474
35°	29848
40°	21583
45°	13645
50°	7437
55°	5161
60°	4868
65°	4514
70°	4296
75°	3728
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13645 cd/sqm



TEST NUMBER: P1281512

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	9.5
10°-20°	74.0	23.0
20°-30°	84.8	26.4
30°-40°	69.2	21.5
40°-50°	34.9	10.9
50°-60°	13.0	4.0
60°-70°	8.7	2.7
70°-80°	4.8	1.5
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.1	58.9
0°-40°	258.2	80.4
0°-60°	306.0	95.3
0°-90°	321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	334	
5°	326	30
15°	266	74
25°	185	85
35°	112	69
45°	44	35
55°	14	13
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1281512
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	334.4
1°	334.0
2°	333.2
3°	331.6
4°	329.2
5°	326.1
6°	322.1
7°	318.1
8°	313.0
9°	307.8
10°	301.9
11°	295.5
12°	288.8
13°	281.2
14°	273.3
15°	265.8
17.5°	245.5
20°	224.9
22.5°	203.9
25°	184.8
27.5°	166.2
30°	148.0
32.5°	129.7
35°	111.5
37.5°	93.2
40°	75.4
42.5°	58.7
45°	44.0
47.5°	31.7
50°	21.8
52.5°	15.9
55°	13.5
57.5°	12.3
60°	11.1
62.5°	9.9
65°	8.7
67.5°	7.5
70°	6.7
72.5°	5.6
75°	4.4
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8



TEST NUMBER: P1281512
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)