

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276869

Luminaire Tested: P3AS20R459835D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276869  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R459835D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 678.0 lumens  
Efficiency: N/A  
Efficacy: 24.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276869  
CATALOG NUMBER: P3AS20R459835D010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276869

CATALOG NUMBER: P3AS20R459835D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	143760
5°	141206
10°	133620
15°	121862
20°	107763
25°	93586
30°	80316
35°	66923
40°	49865
45°	30546
50°	14123
55°	11049
60°	10613
65°	9755
70°	9040
75°	8642
80°	7956
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30546 cd/sqm



TEST NUMBER: P1276869  
 CATALOG NUMBER: P3AS20R459835D010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.9	8.8
10°-20°	149.5	22.0
20°-30°	177.6	26.2
30°-40°	154.3	22.8
40°-50°	77.4	11.4
50°-60°	26.9	4.0
60°-70°	18.9	2.8
70°-80°	10.5	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.0	57.1
0°-40°	541.2	79.8
0°-60°	645.5	95.2
0°-90°	678.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	678.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	656	
5°	642	60
15°	537	149
25°	387	178
35°	250	154
45°	98	77
55°	29	27
65°	19	19
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P1276869  
CATALOG NUMBER: P3AS20R459835D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	655.6
2.5°	652.4
5°	641.5
7.5°	624.3
10°	600.1
12.5°	570.4
15°	536.8
17.5°	499.3
20°	461.8
22.5°	423.5
25°	386.8
27.5°	351.6
30°	317.2
32.5°	284.4
35°	250.0
37.5°	213.3
40°	174.2
42.5°	136.0
45°	98.5
47.5°	64.9
50°	41.4
52.5°	32.0
55°	28.9
57.5°	26.6
60°	24.2
62.5°	21.9
65°	18.8
67.5°	16.4
70°	14.1
72.5°	11.7
75°	10.2
77.5°	7.8
80°	6.3
82.5°	4.7
85°	2.3
87.5°	1.6
90°	0.0

(END OF REPORT)