

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281543

Luminaire Tested: P3AS05R35B2750DE010 E3DLP1WH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1281543  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35B2750DE010 E3DLP1WH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 411.0 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281543  
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1WH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1281543  
 CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1WH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	207286
5°	199229
10°	173588
15°	132941
20°	88954
25°	53834
30°	30891
35°	17266
40°	9189
45°	4714
50°	2252
55°	1797
60°	1710
65°	1401
70°	1475
75°	1356
80°	1515
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4714 cd/sqm



TEST NUMBER: P1281543

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.3	20.0
10°-20°	159.6	38.8
20°-30°	104.5	25.4
30°-40°	42.4	10.3
40°-50°	12.7	3.1
50°-60°	4.3	1.1
60°-70°	2.9	0.7
70°-80°	1.7	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.4	84.3
0°-40°	388.8	94.6
0°-60°	405.8	98.7
0°-90°	411.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	411.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	945	
5°	905	82
15°	586	160
25°	222	104
35°	64	42
45°	15	13
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1281543  
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	945.3
1°	943.8
2°	939.5
3°	930.9
4°	920.7
5°	905.1
6°	885.5
7°	863.6
8°	839.0
9°	810.8
10°	779.6
11°	744.8
12°	708.4
13°	667.7
14°	629.0
15°	585.6
17.5°	480.5
20°	381.2
22.5°	293.2
25°	222.5
27.5°	165.8
30°	122.0
32.5°	89.5
35°	64.5
37.5°	45.7
40°	32.1
42.5°	22.3
45°	15.2
47.5°	10.2
50°	6.6
52.5°	5.1
55°	4.7
57.5°	4.3
60°	3.9
62.5°	3.5
65°	2.7
67.5°	2.3
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.2
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1281543  
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1WH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)