

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281593

Luminaire Tested: P3AS05R40B2750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3CD1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 550.1 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281593

CATALOG NUMBER: P3AS05R40B2750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281593

CATALOG NUMBER: P3AS05R40B2750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0								0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		50	30	10		50	30	10		50	30	10		0
RCR																																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100												
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98		96												
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94		92												
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		94	92	90		89												
4	103	97	93	90	102	96	92	89	94	91	88		92	90	87		91	88	86		85												
5	100	93	89	86	98	92	88	85	91	87	85		89	86	84		88	85	83		82												
6	96	90	85	82	95	89	85	82	88	84	81		86	83	81		85	82	80		79												
7	93	86	82	79	92	86	81	78	85	81	78		83	80	78		82	79	77		76												
8	90	83	79	76	89	83	78	75	82	78	75		81	77	75		80	77	75		73												
9	87	80	76	73	87	80	76	73	79	75	72		78	75	72		77	74	72		71												
10	85	77	73	70	84	77	73	70	76	73	70		76	72	70		75	72	70		69												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289582
5°	288201
10°	278797
15°	246676
20°	160944
25°	57003
30°	12103
35°	3989
40°	1460
45°	496
50°	409
55°	459
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 672 cd/sqm

TEST NUMBER: P1281593

CATALOG NUMBER: P3AS05R40B2750DE010 E3CD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.2	22.4
10°-20°	286.9	52.2
20°-30°	124.5	22.6
30°-40°	11.5	2.1
40°-50°	1.6	0.3
50°-60°	1.0	0.2
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.6	97.2
0°-40°	546.1	99.3
0°-60°	548.7	99.8
0°-90°	550.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	550.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1321	
5°	1309	123
15°	1087	287
25°	236	125
35°	15	11
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281593

CATALOG NUMBER: P3AS05R40B2750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1320.6
2.5°	1319.1
5°	1309.3
7.5°	1288.5
10°	1252.1
12.5°	1190.7
15°	1086.6
17.5°	914.0
20°	689.7
22.5°	447.8
25°	235.6
27.5°	101.4
30°	47.8
32.5°	25.8
35°	14.9
37.5°	9.0
40°	5.1
42.5°	2.7
45°	1.6
47.5°	1.2
50°	1.2
52.5°	1.2
55°	1.2
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)