

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276910

Luminaire Tested: P3AS20R559835D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559835D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2121.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276910

CATALOG NUMBER: P3AS20R559835D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1276910

CATALOG NUMBER: P3AS20R559835D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	588264
5°	582807
10°	606223
15°	597801
20°	551251
25°	448526
30°	272447
35°	94308
40°	26908
45°	12839
50°	5424
55°	2447
60°	2807
65°	2491
70°	2052
75°	2711
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12839 cd/sqm

TEST NUMBER: P1276910

CATALOG NUMBER: P3AS20R559835D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.0	12.1
10°-20°	731.9	34.5
20°-30°	815.9	38.5
30°-40°	266.9	12.6
40°-50°	35.2	1.7
50°-60°	7.5	0.4
60°-70°	4.3	0.2
70°-80°	2.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1803.7	85.0
0°-40°	2070.7	97.6
0°-60°	2113.3	99.6
0°-90°	2121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2683	
5°	2648	256
15°	2633	732
25°	1854	816
35°	352	267
45°	41	35
55°	6	7
65°	5	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1276910

CATALOG NUMBER: P3AS20R559835D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2682.7
2.5°	2663.6
5°	2647.7
7.5°	2685.9
10°	2722.6
12.5°	2703.4
15°	2633.3
17.5°	2521.7
20°	2362.3
22.5°	2142.4
25°	1853.8
27.5°	1487.2
30°	1076.0
32.5°	659.9
35°	352.3
37.5°	178.5
40°	94.0
42.5°	60.6
45°	41.4
47.5°	28.7
50°	15.9
52.5°	9.6
55°	6.4
57.5°	6.4
60°	6.4
62.5°	4.8
65°	4.8
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)