

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276926

Luminaire Tested: P3AS20R559835D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559835D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1737.0 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276926

CATALOG NUMBER: P3AS20R559835D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1276926

CATALOG NUMBER: P3AS20R559835D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	476957
5°	472132
10°	455948
15°	421433
20°	363682
25°	287242
30°	203753
35°	131383
40°	78919
45°	44470
50°	23914
55°	8525
60°	7675
65°	7420
70°	7181
75°	6778
80°	6061
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44470 cd/sqm

TEST NUMBER: P1276926

CATALOG NUMBER: P3AS20R559835D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.7	11.6
10°-20°	513.4	29.6
20°-30°	538.0	31.0
30°-40°	313.9	18.1
40°-50°	117.5	6.8
50°-60°	27.6	1.6
60°-70°	14.2	0.8
70°-80°	8.4	0.5
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1253.1	72.1
0°-40°	1566.9	90.2
0°-60°	1712.0	98.6
0°-90°	1737.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1737.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2175	
5°	2145	202
15°	1856	513
25°	1187	538
35°	491	314
45°	143	117
55°	22	28
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1276926

CATALOG NUMBER: P3AS20R559835D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2175.1
2.5°	2168.8
5°	2144.9
7.5°	2106.6
10°	2047.7
12.5°	1964.8
15°	1856.4
17.5°	1719.4
20°	1558.5
22.5°	1378.4
25°	1187.2
27.5°	991.2
30°	804.7
32.5°	635.8
35°	490.8
37.5°	372.9
40°	275.7
42.5°	197.6
45°	143.4
47.5°	103.6
50°	70.1
52.5°	39.8
55°	22.3
57.5°	19.1
60°	17.5
62.5°	15.9
65°	14.3
67.5°	12.7
70°	11.2
72.5°	9.6
75°	8.0
77.5°	6.4
80°	4.8
82.5°	3.2
85°	1.6
87.5°	1.6
90°	0.0

(END OF REPORT)