

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276939

Luminaire Tested: P3AS20R609835D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609835D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2061.1 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276939

CATALOG NUMBER: P3AS20R609835D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1276939

CATALOG NUMBER: P3AS20R609835D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	492154
5°	472638
10°	486609
15°	492875
20°	435205
25°	366771
30°	297463
35°	193729
40°	88967
45°	34112
50°	11428
55°	3058
60°	2807
65°	2491
70°	2052
75°	2711
80°	2020
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34112 cd/sqm

TEST NUMBER: P1276939

CATALOG NUMBER: P3AS20R609835D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.7	10.0
10°-20°	594.5	28.8
20°-30°	693.5	33.6
30°-40°	447.5	21.7
40°-50°	100.3	4.9
50°-60°	10.0	0.5
60°-70°	4.8	0.2
70°-80°	2.7	0.1
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1494.7	72.5
0°-40°	1942.1	94.2
0°-60°	2052.5	99.6
0°-90°	2061.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2061.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2244	
5°	2147	207
15°	2171	595
25°	1516	693
35°	724	447
45°	110	100
55°	8	10
65°	5	5
75°	3	3
85°	2	1
90°	0	

TEST NUMBER: P1276939

CATALOG NUMBER: P3AS20R609835D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2244.4
2.5°	2207.7
5°	2147.2
7.5°	2144.0
10°	2185.4
12.5°	2212.5
15°	2171.1
17.5°	2046.7
20°	1865.0
22.5°	1675.3
25°	1515.9
27.5°	1359.7
30°	1174.8
32.5°	958.0
35°	723.7
37.5°	494.2
40°	310.8
42.5°	186.5
45°	110.0
47.5°	63.8
50°	33.5
52.5°	11.2
55°	8.0
57.5°	6.4
60°	6.4
62.5°	4.8
65°	4.8
67.5°	4.8
70°	3.2
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

(END OF REPORT)