

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281686

Luminaire Tested: P3AS05R40B2750DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 153.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281686

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281686

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	91		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		87
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47650
5°	46687
10°	43464
15°	37866
20°	30523
25°	22888
30°	16078
35°	10547
40°	6383
45°	3814
50°	2286
55°	1835
60°	1623
65°	1401
70°	1346
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3814 cd/sqm

TEST NUMBER: P1281686

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.7	12.9
10°-20°	46.0	30.0
20°-30°	43.3	28.3
30°-40°	25.0	16.4
40°-50°	10.0	6.5
50°-60°	4.4	2.9
60°-70°	2.7	1.8
70°-80°	1.4	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.0	71.2
0°-40°	134.0	87.6
0°-60°	148.4	97.0
0°-90°	153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	212	20
15°	167	46
25°	95	43
35°	39	25
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281686

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.3
2.5°	216.0
5°	212.1
7.5°	204.8
10°	195.2
12.5°	182.3
15°	166.8
17.5°	149.6
20°	130.8
22.5°	112.1
25°	94.6
27.5°	78.3
30°	63.5
32.5°	50.6
35°	39.4
37.5°	29.8
40°	22.3
42.5°	16.7
45°	12.3
47.5°	9.0
50°	6.7
52.5°	5.4
55°	4.8
57.5°	4.4
60°	3.7
62.5°	3.1
65°	2.7
67.5°	2.3
70°	2.1
72.5°	1.7
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)