

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276950

Luminaire Tested: P3AS20R609835D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609835D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 822.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276950
CATALOG NUMBER: P3AS20R609835D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1276950
 CATALOG NUMBER: P3AS20R609835D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194107
5°	192273
10°	186659
15°	174870
20°	154783
25°	129491
30°	101484
35°	73615
40°	48977
45°	30515
50°	16511
55°	4779
60°	4473
65°	4047
70°	4039
75°	3982
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30515 cd/sqm



TEST NUMBER: P1276950
 CATALOG NUMBER: P3AS20R609835D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.3	10.0
10°-20°	213.7	26.0
20°-30°	243.6	29.6
30°-40°	172.7	21.0
40°-50°	78.4	9.5
50°-60°	16.6	2.0
60°-70°	8.0	1.0
70°-80°	5.0	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.6	65.6
0°-40°	712.3	86.7
0°-60°	807.3	98.2
0°-90°	822.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	885	
5°	874	82
15°	770	214
25°	535	244
35°	275	173
45°	98	78
55°	12	17
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1276950
CATALOG NUMBER: P3AS20R609835D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	885.2
2.5°	882.0
5°	873.5
7.5°	858.6
10°	838.3
12.5°	809.4
15°	770.3
17.5°	721.1
20°	663.3
22.5°	600.8
25°	535.2
27.5°	468.0
30°	400.8
32.5°	336.7
35°	275.0
37.5°	220.3
40°	171.1
42.5°	129.7
45°	98.4
47.5°	73.4
50°	48.4
52.5°	22.7
55°	12.5
57.5°	10.9
60°	10.2
62.5°	9.4
65°	7.8
67.5°	7.0
70°	6.3
72.5°	5.5
75°	4.7
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)