

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281711

Luminaire Tested: P3AS05R40B2750DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 312.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281711
CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281711

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	94	97	94	91	94	92	89	92	89	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69				69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97141
5°	95179
10°	88620
15°	77231
20°	62259
25°	46648
30°	32815
35°	21496
40°	13024
45°	7784
50°	4640
55°	3747
60°	3333
65°	2854
70°	2693
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7784 cd/sqm



TEST NUMBER: P1281711

CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	12.9
10°-20°	93.7	30.0
20°-30°	88.3	28.3
30°-40°	51.1	16.4
40°-50°	20.4	6.5
50°-60°	9.0	2.9
60°-70°	5.6	1.8
70°-80°	2.9	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.2	71.2
0°-40°	273.2	87.6
0°-60°	302.6	97.0
0°-90°	312.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	312.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	443	
5°	432	40
15°	340	94
25°	193	88
35°	80	51
45°	25	20
55°	10	9
65°	6	6
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1281711
CATALOG NUMBER: P3AS05R40B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	443.0
2.5°	440.5
5°	432.4
7.5°	417.6
10°	398.0
12.5°	371.7
15°	340.2
17.5°	305.0
20°	266.8
22.5°	228.5
25°	192.8
27.5°	159.7
30°	129.6
32.5°	103.2
35°	80.3
37.5°	60.7
40°	45.5
42.5°	34.0
45°	25.1
47.5°	18.3
50°	13.6
52.5°	11.0
55°	9.8
57.5°	8.9
60°	7.6
62.5°	6.4
65°	5.5
67.5°	4.7
70°	4.2
72.5°	3.4
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)