

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281792

Luminaire Tested: P3AS05R45B2750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45B2750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 345.0 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281792
CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281792
 CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91	91	91	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83	83	83	83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75	75	75	75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73152
5°	71847
10°	68001
15°	61998
20°	54838
25°	47616
30°	40867
35°	34050
40°	25390
45°	15536
50°	7198
55°	5620
60°	5394
65°	4929
70°	4616
75°	4406
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15536 cd/sqm



TEST NUMBER: P1281792
 CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	8.8
10°-20°	76.0	22.0
20°-30°	90.4	26.2
30°-40°	78.5	22.8
40°-50°	39.4	11.4
50°-60°	13.7	4.0
60°-70°	9.6	2.8
70°-80°	5.4	1.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.9	57.1
0°-40°	275.4	79.8
0°-60°	328.4	95.2
0°-90°	345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	345.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	334	
5°	326	30
15°	273	76
25°	197	90
35°	127	78
45°	50	39
55°	15	14
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1281792
CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	333.6
2.5°	332.0
5°	326.4
7.5°	317.7
10°	305.4
12.5°	290.2
15°	273.1
17.5°	254.1
20°	235.0
22.5°	215.5
25°	196.8
27.5°	178.9
30°	161.4
32.5°	144.7
35°	127.2
37.5°	108.5
40°	88.7
42.5°	69.2
45°	50.1
47.5°	33.0
50°	21.1
52.5°	16.3
55°	14.7
57.5°	13.5
60°	12.3
62.5°	11.1
65°	9.5
67.5°	8.3
70°	7.2
72.5°	6.0
75°	5.2
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)