

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276989

Luminaire Tested: P3AS20R659835D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659835D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1255.0 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276989
CATALOG NUMBER: P3AS20R659835D010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276989
 CATALOG NUMBER: P3AS20R659835D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	223337
5°	220316
10°	212933
15°	200818
20°	185213
25°	168131
30°	148909
35°	126726
40°	100817
45°	71170
50°	41312
55°	22556
60°	20963
65°	19042
70°	17375
75°	16182
80°	14143
85°	12077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 71170 cd/sqm



TEST NUMBER: P1276989
 CATALOG NUMBER: P3AS20R659835D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	7.5
10°-20°	247.5	19.7
20°-30°	318.0	25.3
30°-40°	294.2	23.4
40°-50°	177.6	14.2
50°-60°	60.6	4.8
60°-70°	36.5	2.9
70°-80°	20.6	1.6
80°-90°	5.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.7	52.6
0°-40°	953.9	76.0
0°-60°	1192.0	95.0
0°-90°	1255.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1255.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1018	
5°	1001	94
15°	885	247
25°	695	318
35°	473	294
45°	230	178
55°	59	61
65°	37	36
75°	19	21
85°	5	6
90°	0	



TEST NUMBER: P1276989

CATALOG NUMBER: P3AS20R659835D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1018.5
2.5°	1013.7
5°	1000.9
7.5°	981.8
10°	956.3
12.5°	924.4
15°	884.6
17.5°	841.6
20°	793.7
22.5°	744.3
25°	694.9
27.5°	642.3
30°	588.1
32.5°	533.9
35°	473.4
37.5°	414.4
40°	352.2
42.5°	290.1
45°	229.5
47.5°	173.7
50°	121.1
52.5°	76.5
55°	59.0
57.5°	52.6
60°	47.8
62.5°	41.4
65°	36.7
67.5°	31.9
70°	27.1
72.5°	23.9
75°	19.1
77.5°	15.9
80°	11.2
82.5°	8.0
85°	4.8
87.5°	3.2
90°	0.0

(END OF REPORT)