

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281842

Luminaire Tested: P3AS05R50B2750DE010 E3CB1MMS\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1281842  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R50B2750DE010 E3CB1MMS\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 544.0 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281842

CATALOG NUMBER: P3AS05R50B2750DE010 E3CB1MMS\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1281842

CATALOG NUMBER: P3AS05R50B2750DE010 E3CB1MMS\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  | 102 | 101 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |
| 3   | 105 | 99  | 95  | 91  |  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 94  | 88  | 83  | 79  |  | 86  | 82  | 79  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |
| 6   | 92  | 84  | 79  | 75  |  | 91  | 83  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |
| 7   | 88  | 80  | 75  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 8   | 85  | 76  | 71  | 67  |  | 83  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 66  |
| 9   | 81  | 73  | 68  | 64  |  | 80  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 71  | 66  | 63  |  | 70  | 66  | 63  |
| 10  | 78  | 69  | 64  | 61  |  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  | 63  | 61  |  | 67  | 63  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 189459 |
| 5°  | 186066 |
| 10° | 178665 |
| 15° | 163837 |
| 20° | 144469 |
| 25° | 110716 |
| 30° | 60212  |
| 35° | 19381  |
| 40° | 4551   |
| 45° | 620    |
| 50° | 546    |
| 55° | 612    |
| 60° | 526    |
| 65° | 623    |
| 70° | 513    |
| 75° | 678    |
| 80° | 505    |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 85°  
Luminance: 1006 cd/sqm

TEST NUMBER: P1281842

CATALOG NUMBER: P3AS05R50B2750DE010 E3CB1MMS\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 79.3   | 14.6      |
| 10°-20°   | 200.6  | 36.9      |
| 20°-30°   | 200.9  | 36.9      |
| 30°-40°   | 56.5   | 10.4      |
| 40°-50°   | 3.4    | 0.6       |
| 50°-60°   | 1.3    | 0.2       |
| 60°-70°   | 1.0    | 0.2       |
| 70°-80°   | 0.7    | 0.1       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 480.8  | 88.4      |
| 0°-40°    | 537.3  | 98.8      |
| 0°-60°    | 542.0  | 99.6      |
| 0°-90°    | 544.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 544.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 864 |      |
| 5°  | 845 | 79   |
| 15° | 722 | 201  |
| 25° | 458 | 201  |
| 35° | 72  | 56   |
| 45° | 2   | 3    |
| 55° | 2   | 1    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1281842

CATALOG NUMBER: P3AS05R50B2750DE010 E3CB1MMS\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 864.0 |
| 2.5°  | 859.6 |
| 5°    | 845.3 |
| 7.5°  | 825.8 |
| 10°   | 802.4 |
| 12.5° | 767.0 |
| 15°   | 721.7 |
| 17.5° | 669.6 |
| 20°   | 619.1 |
| 22.5° | 556.3 |
| 25°   | 457.6 |
| 27.5° | 340.7 |
| 30°   | 237.8 |
| 32.5° | 143.5 |
| 35°   | 72.4  |
| 37.5° | 34.2  |
| 40°   | 15.9  |
| 42.5° | 6.0   |
| 45°   | 2.0   |
| 47.5° | 1.6   |
| 50°   | 1.6   |
| 52.5° | 1.6   |
| 55°   | 1.6   |
| 57.5° | 1.2   |
| 60°   | 1.2   |
| 62.5° | 1.2   |
| 65°   | 1.2   |
| 67.5° | 0.8   |
| 70°   | 0.8   |
| 72.5° | 0.8   |
| 75°   | 0.8   |
| 77.5° | 0.4   |
| 80°   | 0.4   |
| 82.5° | 0.4   |
| 85°   | 0.4   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)