

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1277007

Luminaire Tested: P3AS20R709835D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1277007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709835D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1901.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1277007

CATALOG NUMBER: P3AS20R709835D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1277007

CATALOG NUMBER: P3AS20R709835D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	369641
5°	348535
10°	330477
15°	324542
20°	312834
25°	294888
30°	292779
35°	254977
40°	164938
45°	77962
50°	10916
55°	879
60°	702
65°	830
70°	513
75°	678
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 77962 cd/sqm

TEST NUMBER: P1277007

CATALOG NUMBER: P3AS20R709835D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	7.8
10°-20°	401.5	21.1
20°-30°	567.9	29.9
30°-40°	570.8	30.0
40°-50°	205.3	10.8
50°-60°	5.5	0.3
60°-70°	1.3	0.1
70°-80°	0.8	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1117.3	58.8
0°-40°	1688.0	88.8
0°-60°	1898.8	99.9
0°-90°	1901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1686	
5°	1583	148
15°	1430	401
25°	1219	568
35°	952	571
45°	251	205
55°	2	6
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1277007

CATALOG NUMBER: P3AS20R709835D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1685.7
1°	1681.0
2°	1666.2
3°	1642.7
4°	1613.1
5°	1583.4
6°	1555.3
7°	1533.4
8°	1513.9
9°	1498.3
10°	1484.2
11°	1472.5
12°	1461.6
13°	1450.7
14°	1440.5
15°	1429.6
16°	1416.3
17°	1402.3
18°	1385.1
19°	1364.0
20°	1340.6
21°	1314.8
22°	1289.0
23°	1264.1
24°	1239.9
25°	1218.8
26°	1203.9
27°	1192.2
28°	1182.9
29°	1171.9
30°	1156.3
31°	1133.7
32°	1101.7
32.5°	1083.7
33°	1059.5
34°	1011.9
35°	952.5
36°	887.0
37°	812.8
37.5°	778.4
38°	731.6
39°	648.0
40°	576.2
42.5°	399.0
45°	251.4



TEST NUMBER: P1277007

CATALOG NUMBER: P3AS20R709835D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	135.1
50°	32.0
52.5°	3.9
55°	2.3
57.5°	2.3
60°	1.6
62.5°	1.6
65°	1.6
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)