

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281856

Luminaire Tested: P3AS05R50B2750DE010 E3CD1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R50B2750DE010 E3CD1MB_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 80CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 582.1 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281856

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MB_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281856

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MB_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202703
5°	199075
10°	191134
15°	175279
20°	154550
25°	118458
30°	64415
35°	20719
40°	4866
45°	651
50°	580
55°	650
60°	570
65°	675
70°	577
75°	763
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 1006 cd/sqm

TEST NUMBER: P1281856

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.9	14.6
10°-20°	214.6	36.9
20°-30°	214.9	36.9
30°-40°	60.4	10.4
40°-50°	3.6	0.6
50°-60°	1.4	0.2
60°-70°	1.1	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.4	88.4
0°-40°	574.9	98.8
0°-60°	579.9	99.6
0°-90°	582.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	924	
5°	904	85
15°	772	215
25°	490	215
35°	77	60
45°	2	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1281856

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MB_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	924.4
2.5°	919.7
5°	904.4
7.5°	883.5
10°	858.4
12.5°	820.6
15°	772.1
17.5°	716.3
20°	662.3
22.5°	595.1
25°	489.6
27.5°	364.6
30°	254.4
32.5°	153.6
35°	77.4
37.5°	36.6
40°	17.0
42.5°	6.4
45°	2.1
47.5°	1.7
50°	1.7
52.5°	1.7
55°	1.7
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)