

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1280872

Luminaire Tested: P3AS05R15B2750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1280872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15B2750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 202.1 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1280872

CATALOG NUMBER: P3AS05R15B2750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1280872

CATALOG NUMBER: P3AS05R15B2750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95											
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91											
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87											
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83											
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80											
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77											
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74											
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	71											
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69											
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172552
5°	153180
10°	106366
15°	62906
20°	35820
25°	20469
30°	11344
35°	6050
40°	3349
45°	1799
50°	1126
55°	879
60°	789
65°	726
70°	641
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1799 cd/sqm

TEST NUMBER: P1280872

CATALOG NUMBER: P3AS05R15B2750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	29.3
10°-20°	78.1	38.6
20°-30°	40.2	19.9
30°-40°	15.1	7.5
40°-50°	4.9	2.4
50°-60°	2.1	1.0
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.5	87.8
0°-40°	192.6	95.3
0°-60°	199.6	98.8
0°-90°	202.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	202.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	787	
5°	696	59
15°	277	78
25°	85	40
35°	23	15
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1280872

CATALOG NUMBER: P3AS05R15B2750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	786.9
1°	785.4
2°	775.1
3°	755.4
4°	729.5
5°	695.9
6°	657.7
7°	615.9
8°	569.4
9°	523.5
10°	477.7
12.5°	367.6
15°	277.1
17.5°	207.4
20°	153.5
22.5°	114.6
25°	84.6
27.5°	61.7
30°	44.8
32.5°	31.7
35°	22.6
37.5°	16.2
40°	11.7
42.5°	8.4
45°	5.8
47.5°	4.3
50°	3.3
52.5°	2.7
55°	2.3
57.5°	1.9
60°	1.8
62.5°	1.6
65°	1.4
67.5°	1.2
70°	1.0
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)