

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281975

Luminaire Tested: P3AS05R50B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R50B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 448.1 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281975

CATALOG NUMBER: P3AS05R50B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281975

CATALOG NUMBER: P3AS05R50B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142642
5°	139753
10°	130904
15°	117186
20°	98615
25°	75270
30°	48919
35°	28991
40°	16774
45°	8404
50°	3138
55°	2447
60°	2281
65°	2075
70°	2052
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8404 cd/sqm

TEST NUMBER: P1281975

CATALOG NUMBER: P3AS05R50B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	13.2
10°-20°	142.8	31.9
20°-30°	140.1	31.3
30°-40°	70.6	15.7
40°-50°	22.3	5.0
50°-60°	5.8	1.3
60°-70°	4.1	0.9
70°-80°	2.5	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.9	76.3
0°-40°	412.5	92.1
0°-60°	440.6	98.3
0°-90°	448.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	650	
5°	635	59
15°	516	143
25°	311	140
35°	108	71
45°	27	22
55°	6	6
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1281975

CATALOG NUMBER: P3AS05R50B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	650.5
2.5°	646.5
5°	634.9
7.5°	614.2
10°	587.9
12.5°	554.1
15°	516.2
17.5°	472.4
20°	422.6
22.5°	368.9
25°	311.1
27.5°	249.8
30°	193.2
32.5°	145.4
35°	108.3
37.5°	80.1
40°	58.6
42.5°	41.4
45°	27.1
47.5°	15.5
50°	9.2
52.5°	6.8
55°	6.4
57.5°	5.6
60°	5.2
62.5°	4.8
65°	4.0
67.5°	3.6
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)