

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1280903

Luminaire Tested: P3AS05R15B2750DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1280903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15B2750DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 151.0 lumens
Efficiency: N/A
Efficacy: 25.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1280903

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1280903

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38089
5°	37046
10°	33867
15°	29671
20°	25436
25°	21243
30°	16990
35°	12742
40°	9246
45°	6047
50°	3787
55°	2561
60°	2281
65°	2075
70°	1988
75°	1779
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6047 cd/sqm

TEST NUMBER: P1280903

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.5	10.3
10°-20°	36.4	24.1
20°-30°	40.1	26.6
30°-40°	30.0	19.9
40°-50°	15.6	10.3
50°-60°	6.4	4.3
60°-70°	4.0	2.6
70°-80°	2.2	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	92.0	61.0
0°-40°	122.1	80.9
0°-60°	144.1	95.4
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	174	
5°	168	16
15°	131	36
25°	88	40
35°	48	30
45°	20	16
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1280903

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	173.7
1°	173.9
2°	173.3
3°	172.2
4°	170.4
5°	168.3
6°	165.7
7°	162.8
8°	159.3
9°	155.7
10°	152.1
12.5°	141.6
15°	130.7
17.5°	119.7
20°	109.0
22.5°	98.1
25°	87.8
27.5°	77.5
30°	67.1
32.5°	57.0
35°	47.6
37.5°	39.6
40°	32.3
42.5°	25.6
45°	19.5
47.5°	14.7
50°	11.1
52.5°	8.2
55°	6.7
57.5°	5.9
60°	5.2
62.5°	4.6
65°	4.0
67.5°	3.4
70°	3.1
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)