

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281992

Luminaire Tested: P3AS05R55B2750DE010 E3CB1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3CB1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281992

CATALOG NUMBER: P3AS05R55B2750DE010 E3CB1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281992

CATALOG NUMBER: P3AS05R55B2750DE010 E3CB1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146436
5°	145080
10°	150921
15°	148809
20°	137235
25°	111660
30°	67808
35°	23477
40°	6698
45°	3194
50°	1365
55°	612
60°	702
65°	623
70°	513
75°	678
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3194 cd/sqm

TEST NUMBER: P1281992

CATALOG NUMBER: P3AS05R55B2750DE010 E3CB1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	12.1
10°-20°	182.2	34.5
20°-30°	203.1	38.5
30°-40°	66.4	12.6
40°-50°	8.8	1.7
50°-60°	1.9	0.4
60°-70°	1.1	0.2
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.0	85.0
0°-40°	515.5	97.6
0°-60°	526.1	99.6
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	659	64
15°	656	182
25°	462	203
35°	88	66
45°	10	9
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281992

CATALOG NUMBER: P3AS05R55B2750DE010 E3CB1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	667.8
2.5°	663.1
5°	659.1
7.5°	668.6
10°	677.8
12.5°	673.0
15°	655.5
17.5°	627.8
20°	588.1
22.5°	533.3
25°	461.5
27.5°	370.2
30°	267.8
32.5°	164.3
35°	87.7
37.5°	44.4
40°	23.4
42.5°	15.1
45°	10.3
47.5°	7.1
50°	4.0
52.5°	2.4
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.2
65°	1.2
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)